



America

CERTIFICATE

No. Z1US 065527 0034 Rev. 00

Holder of Certificate: **Bullfrog International, LC**
668 West 14600 South
Bluffdale UT 84065
USA

Certification Mark:



Product: Whirlpool spa
(Spa)

Model(s): A5L-E, A6-E, A6L-E, A7-E, A7L-E, A8-E, A8D-E, A8L-E, A9L-E, R5L-E, R6-E, R6L-E, R7-E, R7L-E, R8-E, R8L-E, STIL5-E, STIL7-E, X5L-E, X6L-E, X6R-E, X7-E, X7L-E, X8-E, X8L-E, M7E, M8D, M9T

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

Test report no.: 231-72144470-100

Valid until: 2025-03-11

Date, 2020-04-20 (Adrian Rabago Valenzuela)

~~Ret.~~



America

CERTIFICATE

No. Z1US 065527 0034 Rev. 00

Brand Name: bullfrog spas, Villeroy & Boch

Tested according to: EN 60335-1:2012
EN 60335-2-60:2003/A12:2010
EN 50366:2003/A1:2009

Production Facility(ies): 065527

Parameters:

Rated Input Voltage: 230 VAC or 230 VAC x 2 (Single phase) or 400 VAC (3 phase)
Rated Frequency: 50 Hz
Rated Input Current: 230 VAC: 16/32 A
230 VAC x 2 (Single phase): 16 A x 2
230 VAC x 2 (Single phase) (A9L-E only): 20 A x 2
400 VAC (3 phase): 16 A x 3
230 VAC 50 Hz (M7E): 16 A x 2, 16 A x 3, 16/32 A
230 VAC 50 Hz (M8D & M9T): 20 A x 2, 40 A
Protection Class: Class I
Degree of Protection: IPX5
Temperature, Ambient: -30°C to 45°C

See below for additional model information

Model Differences:

All models are similar in electrical control circuit. The differences are in seat configuration, volume, size, and pump numbers as specified in table below.

Options: Ozone Generator

Installation Requirements:

When installing the equipment, all requirements of the standard and manufacturer's specifications must be met. The models require:

- The spa must be connected to a Ground Fault Circuit Interrupter (GFCI)
- The GFCI should be approved product with a maximum 30 mA tripping current or less to meet the national and local rules. Always test the GFCI before use.
- The Spas must be wired in accordance with applicable national and local electrical codes, All Electrical work should be done by experienced, licensed electrician.
- The ground terminal should be bonded with a min 8.4 mm² (8 AWG) solid copper wire between this unit and any metal ladders, metal water pipes etc within 1.5m of the spa.
- Prevent any electrical appliance within 1.5m of the spa.

Manufacturer's warning statements / misuse:

Extreme caution must be exercised to prevent unauthorized access by children.

Side effects of medication may increase by using the spa, consult a physician beforehand.

Pregnant women or persons suffering from some kind of diseases should consult a physician before using spa.



America

CERTIFICATE

No. Z1US 065527 0034 Rev. 00

Model Variant

Models	Dimension W x D x H (m)	Seating Capacity	Capacity(L)	Dry Weight(kg)	Filled Weight (kg)	No. of Pumps / Hp
A5L-E	1.73 x 2.08 x 0.79	3	920	206	1,395	2/2.5 or 2.0
A6-E	2.03 x 2.24 x 0.86	6	1,360	261	2,098	2/2.5 or 2.0
A6L-E	2.03 x 2.24 x 0.86	6	1,324	261	2,064	2/2.5 or 2.0
A7-E	2.24 x 2.24 x 0.91	8	1,666	300	2,404	2/2.5 or 2.0
A7L-E	2.24 x 2.24 x 0.91	6	1,643	308	2,383	2/2.5 or 2.0
A8-E	2.39 x 2.39 x 0.97	8	2,044	344	2,862	2/2.5 or 2.0
A8D-E	2.39 x 2.39 x 0.97	5	1,938	346	2,769	2/2.5 or 2.0
A8L-E	2.39 x 2.39 x 0.97	6	1,908	353	2,746	2/2.5 or 2.0
A9L-E	2.74 x 2.39 x 0.97	8	2,256	412.76	3,147	3/2.0
R5L-E	1.73 x 2.08 x 0.79	3	920	206	1,395	1/2.5 or 2.0
R6-E	2.03 x 2.24 x 0.86	6	1,360	261	2,098	2/2.5 or 2.0
R6L-E	2.03 x 2.24 x 0.86	6	1,688	261	2,338	2/2.5 or 2.0
R7-E	2.24 x 2.24 x 0.91	8	1,666	300	2,404	2/2.5 or 2.0
R7L-E	2.24 x 2.24 x 0.91	6	1,643	308	2,383	2/2.5 or 2.0
R8-E	2.39 x 2.39 x 0.97	8	2,044	344	2,862	2/2.5 or 2.0
R8L-E	2.39 x 2.39 x 0.97	6	1,908	353	2,746	2/2.5 or 2.0
STIL5-E	2.08 x 1.68 x 0.78	4	969	215	1,184	1/2.5 or 2.0
STIL7-E	2.15 x 2.23 x 0.86	6	1,486	279	2,292	1/2.5 or 2.0
X5L-E	1.7 x 2.13 x 0.79	3	920	206	1,395	1/2.5 or 2.0
X6L-E	2.03 x 2.24 x 0.86	6	1,688	261	2,338	1/2.5 or 2.0
X6R-E	2.01 x Round x 0.91	5	1,101	228	1,424	1/2.5 or 2.0
X7-E	2.24 x 2.24 x 0.91	8	1,666	300	2,404	2/2.5 or 2.0
X7L-E	2.24 x 2.24 x 0.91	6	1,643	308	2,383	2/2.5 or 2.0
X8-E	2.39x 2.39 x 0.97	8	2,044	344	2,862	2/2.5 or 2.0
X8L-E	2.03 x 2.24 x 0.86	6	1,908	353	2,746	2/2.5 or 2.0
M7E	2.31 x 2.31 x 0.94	6	1,723	345	2,611	2/2.5 or 2.0
M8D	2.39 x 2.39 x 0.96	6	1,787	378	2743	3/2.0
M9T	2.79 x 2.39 x 0.96	7	2,223	442	3283	3/2.0